## CS524 Battery Powered Tube Sealer with Handle

# Qseal\*auto



#### manufacturer

Conroy Medical AB Valhallavaegen 1 SE-194 63 Upplands Vaesby SWEDEN

#### www.conroy.se

Please, contact your local Conroy Medical representative for more information.



REF CS524: Qseal-auto, a complete sealing system, which includes

Main unit, Hand Unit, Coaxial cable, Battery, Charger and

Operator's manual.

Type of PVC tube: Different types and sizes of tubes up to 6.2 mm outer

diameter can be sealed due to a sophisticated sensing system, which automatically adapts sealing time.

Sealing capacity: Max. 480 seals/hour with PVC tubes up to 5 mm (0.2")

outer diameter at 20 °C (68 °F) 1500 seals/battery loading.

Sealing time: 1-2 sec., max 5 sec. depending on tubing.

Intended Use: The Qseal-auto is a fully automatic system for sealing PVC

tubes connected to blood bags included either in Blood Packs or in Apheresis Disposable Sets. The sealing can be performed when the donor is still connected to the Blood Pack or the Apheresis Disposable Set.

Input Power: Loader: 100-240 V ~ 50/60 Hz

Battery: 28VDC, 2.2Ah, NiMH

Consumption: Loader: 30W Sealer: 295W max

Fuses: Battery: 50A / 158°F (70°C) Automatic fuse

RF Output:  $150 \text{ W max.} / 50 \Omega / 40.680 \text{ MHz}$ 

Pump output: 2 bar max./1.9 liter per minute

Size and weight: Main unit: W: 160 mm (6.3") H: 70 mm (2.8")

D: 260 mm (10") 3.40 kg (7.5 lbs) including battery Hand unit: L: 210 mm (8") Ø: 28 mm (1") 0.22 kg (0.48 lbs)

Temperature: Operating: 15 - 35°C (60 - 95°F)

Storage: -20 - 70°C (-4 - 158°F)

Humidity: Operating: 10 - 90% Rh (non condensing)

Storage: 10 - 90% Rh (non condensing)

Altitude: Operating: maximum 3000 meters (9842 feet)

In compliance with: - EN 60601-1: 2006, General Regirements for basic safety

and essential performance.

- EN 60601-1-2: 2007, Collateral standards for

Electromagnetic Compatibility.

Electrical safety: Class I

The Qseal-auto is used in the same environment as medical equipment (hospitals and blood banks). It must be used by highly qualified personnel.

### CS524 Qseal-auto







#### manufacturer

Conroy Medical AB Valhallavaegen 1 SE-194 63 Upplands Vaesby

**SWEDEN** 

#### distributor / salesman

Please, contact your local Conroy Medical representative for more information. www.conroy.se

